

# CleanSpace™

wearable protective masks



## CLEANSAPCE MASKS

HIGH PROTECTION, FIT AND COMFORT



# WORK EFFORTLESSLY & COMFORTABLY OVER LONG PERIODS WITH P3 PROTECTION



**CleanSpace™**  
**with Full Face Mask\***  
ensures high protection &  
comfort over long periods

\*Note: The Full face Mask is compatible with CleanSpace™ Ultra and CleanSpace™ EX.

## Suitable Applications

- Asbestos removal
- Chemical handling
- First responder

## Features

- Positive pressure
- Easily removed orinasal
- Portacount fit adaptor
- Prescription spec frame
- Tear offs

**SAFE** Fully certified positive pressure respirator with P3 TM3 filtration efficiency ensuring maximum protection in the workplace. Breath responsive. Up to 8 hours run time. Portacount testing enabled.

**WEARABLE** Easy to wear; Effortless and comfortable. No hoses or heavy waist mounted battery packs. Award winning lightweight design (500g) delivers clean fresh air for a full shift.

**SMART** Tough, reliable, cost effective; no servicing or maintenance and easy to clean; A simple one-button system; CleanSpace compact design provides compatibility with other PPE.

## WORK EFFORTLESSLY AND COMFORTABLY WITH 99.97% PROTECTION

CleanSpace is the only choice in protective masks due to its wearability, comfort and one-button simplicity. Now the choice in respiratory safety in over 20 countries.

# FITTING THE CLEANSPACE™ MASKS: A GUIDE

The CleanSpace™ masks and PAPR system is easy to fit and use. It is important that your mask is the right fit for your face and seals correctly. **Mask fitting should be done by a specialist or designated mask fitter.** The fit must be confirmed by a quantitative fit test performed according to Respirator Protection Standards in your territory.


ALL CleanSpace Masks can be portacount tested using the **CleanSpace PortaCount Adaptors.**

NAME	DESCRIPTION	WEIGHT
CleanSpace H Series SMALL	HALF MASK SMALL	125g
CleanSpace H Series MEDIUM	HALF MASK MEDIUM	125g
CleanSpace H Series LARGE	HALF MASK LARGE	150g
CleanSpace Full Face Mask MEDIUM / LARGE	FULL FACE MASK MEDIUM / LARGE	700g




## SELECTING YOUR SIZE FOR THE HALF MASKS

This is a guide to selecting the half mask most likely to fit you. Ensure masks are fit tested by a specialist before use.



FACE LENGTH	103.5mm	First try: MEDIUM* Then try: LARGE	First try: LARGE Then try: MEDIUM	First try: LARGE Then try: MEDIUM	
	103.5mm	First try: MEDIUM Then try: SMALL*	First try: MEDIUM Then try: LARGE	First try: LARGE Then try: MEDIUM	
	103.5mm	First try: SMALL Then try: MEDIUM	First try: MEDIUM Then try: SMALL	First try: MEDIUM Then try: SMALL	
	103.5mm	First try: SMALL Then try: MEDIUM	First try: SMALL Then try: MEDIUM	First try: SMALL Then try: MEDIUM	
	93.5mm	First try: SMALL Then try: MEDIUM	First try: SMALL Then try: MEDIUM	First try: SMALL Then try: MEDIUM	
		34.5mm	43.5mm	52.5mm	61.5mm
		LIP LENGTH			

\* On narrow faces, the action of pulling on the arms of the mask to tighten it causes the height of the mask to increase. The narrower the face, the more likely a smaller mask will be a better fit.



# CLEANSPACE™ POWERED RESPIRATORS: A PRODUCT GUIDE

RESPIRATORY PROTECTION MADE EASY

## POWER UNITS



CLEANSPACE2 PAPER

STANDARD USE



CLEANSPACE ULTRA PAPER

IP RATING 66 – DECONTAMINATION



CLEANSPACE EX PAPER

INTRINSICALLY SAFE



## FACE MASKS



SMALL



MEDIUM



LARGE



FULL FACE\*

## FILTERS



FILTER ADAPTOR



HI CAPACITY (HI CAP)  
PARTICULATE FILTER  
P3 HEPA



EN12942 TM3P HEPA  
PARTICULATE FILTER  
(PACK OF 3)



COMBINED: ORGANIC GAS  
& VAPOUR + PARTICULATE  
AU:A1P3



PRE-FILTER  
(PACK OF 10)



COMBINED: ORGANIC,  
INORGANIC & ACID GAS &  
VAPOUR + PARTICULATE  
AU:ABE1P3

